

Sub-base VMPA2-FB-AP-2-1-T0-RV

Part number: 8034550

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---|
| Width | 52 mm |
| Length | 107.3 mm |
| Width dimension | 21 mm |
| Max. no. of valve positions | 2 |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Pilot pressure MPa | 0.3 MPa ... 0.8 MPa |
| Pilot pressure | 3 bar ... 8 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 190 g |
| Note on materials | RoHS compliant |
| Material of sub-base | Die-cast aluminum |