

Plastic tubing PAN-R-22X2-SW

Part number: 8036207

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	22 mm
Bending radius relevant for flow rate	350 mm
Inside diameter	18 mm
Operating pressure for entire temperature range	-0.095 MPa ... 0.8 MPa
Operating pressure for entire temperature range	-0.95 bar ... 8 bar
Operating pressure for entire temperature range	-13.775 psi ... 116 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.4 MPa
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Temperature-dependent operating pressure	-13.775 psi ... 203 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.131 kg/m
Pneumatic connection	For plug connection outside diameter 22 mm
Color	Black
Shore hardness	D 62 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-A