

# Sub-base VABS-K1-7B-12-M5-P

Part number: 8047064

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	1.2 mm
Valve size	7 mm
Fluid connector	Internal thread M5
Mounting position	Any
Structural design	Connection direction downwards
Flow direction	Reversible
Operating medium	Liquid media Gaseous media
Information on operating and pilot media	Observe resistance of materials that come into contact with media
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
For use in the food industry	See supplementary material information
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Max. tightening torque for valve mounting	0.15 Nm
Max. tightening torque of pneumatic fitting	0.6 Nm
Product weight	3.3 g
Sub-base mounting type	With through-hole
Pneumatic valve mounting type	With internal thread
Note on materials	RoHS-compliant
Material of sub-base	PEEK
Threaded sleeve material	High-alloy stainless steel