

# Fixed flow restrictor VFFG-T-F4-12

Part number: 8047351

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Valve function                           | Flow control function  |
| Type of mounting                         | Tapped   |
| Operating pressure                       | -0.09 MPa ... 1 MPa  |
| Operating pressure                       | -0.9 bar ... 10 bar  |
| Ambient temperature                      | -5 °C ... 60 °C  |
| Certification                            | c UL us - recognized (OL)  |
| Size                                     | For 4 mm diameter  |
| Nominal width                            | 1.2 mm   |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Storage temperature                      | -10 °C ... 60 °C   |
| Product weight                           | 0.4 g  |
| Note on materials                        | RoHS compliant   |