

Fixed flow restrictor VFFG-T-F6-7

Part number: 8047353

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Valve function | Flow control function |
| Type of mounting | Tapped |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Ambient temperature | -5 °C ... 60 °C |
| Certification | c UL us - Recognized (OL) |
| Size | For 5.8 mm diameter |
| Nominal width | 0.7 mm |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Product weight | 1.2 g |
| Note on materials | RoHS-compliant |