

Non return valve VABF-L1-10H-H2

Part number: 8047364

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Valve size	10 mm
Valve function	Unlockable check valve function
Operating pressure	0.05 MPa ... 0.8 MPa
Operating pressure	0.5 bar ... 8 bar
Certification	c UL us - Recognized (OL)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 60 °C
Product weight	0.4 g
Type of mounting	Tapped
Note on materials	RoHS-compliant