

# Roller lever VAOM-R4-20-D1-32

Part number: 8049235

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Width	20 mm
Actuation type	Mechanical
Mounting position	Movement level
Structural design	Roller lever
Type of control	directly
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Type of mounting	Screwed on
Note on materials	RoHS compliant
Actuator attachments material	Steel, galvanized