

Toggle roller lever VAOM-R4-20-D2-52

Part number: 8049236



 [General operating condition](#)

Data sheet

Feature	Value
Width	20 mm
Actuation type	Mechanical
Mounting position	Movement plane
Structural design	One-way roller lever
Type of control	Direct
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Type of mounting	Screwed tightly
Note on materials	RoHS-compliant
Actuator attachments material	Steel, galvanized