

# Parallel kit EAMM-U-70-D32-68GA-96

Part number: 8058951

FESTO



 [General operating condition](#)

## Data sheet

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Size                     | 70                    |
| Mounting position        | Any                   |
| Max. rotational speed    | 5000 rpm              |
| LABS (PWIS) conformity   | VDMA24364-B2-L        |
| Storage temperature      | -25 °C ... 60 °C      |
| Relative air humidity    | 0 - 95 %              |
| Degree of protection     | IP40                  |
| Ambient temperature      | -10 °C ... 60 °C      |
| Mass moment of inertia   | 118 kgmm <sup>2</sup> |
| No-load driving torque   | 0.18 Nm               |
| Transferable torque      | 7 Nm                  |
| Product weight           | 1800 g                |
| Interface code, actuator | D32                   |
| Interface code, motor in | 68GA                  |
| Note on materials        | RoHS-compliant        |