


Parallel kit EAMM-U-86-S48-60RB-102

Part number: 8058997

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	86
Mounting position	Any
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	175 kgmm ²
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	2500 g
Interface code, actuator	S48
Interface code, motor in	60RB
Note on materials	RoHS compliant