

Parallel kit EAMM-U-145-S62-126AA-288

Part number: 8059073

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	145
Mounting position	Any
Max. rotational speed	4000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	2270 kgmm ²
No-load driving torque	2 Nm
Transferable torque	9.5 Nm
Product weight	15000 g
Interface code, actuator	S62
Interface code, motor in	126AA
Note on materials	RoHS-compliant