

# Quick coupling plug NPHS-S6-M-G38F

Part number: 8059263

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	7.85 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Normal nominal flow rate (normalized to DIN 1343)	1050 l/min ... 2083 l/min
Nominal flow rate standardized according to ISO 8778	1138.2 l/min ... 2258 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	29 g
Pneumatic connection 1	Internal thread G3/8
Note on materials	RoHS-compliant
Information on materials	Steel, galvanized