


Axial kit EAMM-A-L27-60RA

Part number: 8063452

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	32.1 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	0.45 kgmm ²
Transferable torque	2 Nm
Product weight	298 g
Interface code, actuator	L27
Interface code, motor in	60RA
Note on materials	RoHS compliant