


Axial kit EAMM-A-L62-120GC

Part number: 8063510

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	91.9 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	151 kgmm ²
Transferable torque	47 Nm
Product weight	1931 g
Interface code, actuator	L62
Interface code, motor in	120GC
Note on materials	RoHS-compliant