


Axial kit EAMM-A-M48-50GA

Part number: 8063550

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	22.3 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	39 kgmm ²
Transferable torque	17 Nm
Product weight	422 g
Interface code, actuator	M48
Interface code, motor in	50GA
Note on materials	RoHS compliant