

# Axial kit EAMM-A-N38-88A

Part number: 8063579

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	44.4 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	14.5 kgmm <sup>2</sup>
Transferable torque	12.5 Nm
Product weight	872 g
Interface code, actuator	N38
Interface code, motor in	88A
Note on materials	RoHS compliant