

# Electronics module VMPA14-MPM-EMM-4

Part number: 8066768

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                   | Value             |
|---|-------------------|
| Max. no. of valve positions               | 4                 |
| Max. no. of solenoid coils                | 4                 |
| Nominal pick-up current per solenoid coil | 80 mA to 25 ms    |
| Nominal current with current reduction    | 25 mA after 25 ms |
| Corrosion resistance class (CRC)          | (when installed)  |
| LABS (PWIS) conformity                    | VDMA24364-B1/B2-L |
| Product weight                            | 30 g              |
| Housing material                          | POM               |
| Note on materials                         | RoHS-compliant    |