

Electronics module VMPA14-MPM-EMM-4

Part number: 8066768

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|-------------------|
| Max. no. of valve positions | 4 |
| Max. no. of solenoid coils | 4 |
| Nominal pick-up current per solenoid coil | 80 mA up to 25 ms |
| Nominal current with current reduction | 25 mA after 25 ms |
| Corrosion resistance class (CRC) | (installed) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 30 g |
| Housing material | POM |
| Note on materials | RoHS compliant |