

Shock absorber DYSS-12-12-Y1F

Part number: 8069004

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|-------------------------------|
| Size | 12 |
| Stroke | 12 mm |
| Cushioning | Self-adjusting |
| Mounting position | Any |
| Position sensing | None |
| Symbol | 00991495 |
| Max. impact velocity | 1.5 m/s |
| Reset time at room temperature | 0.2 s |
| Reset time at min. ambient temperature | 1 s |
| Mode of operation | Pushing Single-acting |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -5 °C ... 80 °C |
| Cushioning length | 12 mm |
| Max. stop force | 1000 N |
| Max. tightening torque | 20 Nm |
| Max. energy absorption per stroke | 10 J |
| Max. energy absorption per hour | 36000 J |
| Max. residual energy | 0.05 J |
| Resetting force | 4 N |
| Min. insertion force | 35 N |
| Product weight | 82 g |
| Load range | 45 kg |
| Type of mounting | With lock nut |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Housing material | High-alloy steel |
| Piston rod material | High-alloy steel |