

# Reducing nipple NPFC-R-G12-G14-MF-P50

Part number: 8069232

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Threaded fitting material	Brass, nickel-plated
Pack size	50
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 150 °C
Product weight	31.4 g
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/4
Note on materials	RoHS-compliant