

# Bulkhead fitting NPFC-H-M5-F

Part number: 8069239

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Threaded fitting material        | Brass, nickel-plated                         |
| Pack size                        | 10   |
| Operating pressure               | -0.95 bar ... 50 bar                         |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [-:~:] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                     |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                            |
| Ambient temperature              | -20 °C ... 150 °C                            |
| Product weight                   | 12 g   |
| Pneumatic connection 1           | M5   |
| Pneumatic connection 2           | M5   |
| Note on materials                | RoHS-compliant                               |