

# Operator unit CDSB-A1

Part number: 8070984

FESTO



 General operating condition

## Data sheet

Feature	Value
Max. cable length	3 m
User memory	3 GB
Display	Color TFT
Display properties	Touchscreen
Display size	1.77"
DC operating voltage range	4.5 V ... 5.5 V
Display resolution	128x160 pixels
Certification	RCM compliance mark
KC characters	KC EMC
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
Relative air humidity	Max. 95 % at 60 °C Non-condensing
Degree of protection	IP20
Ambient temperature	0 °C ... 60 °C
Product weight	36.6 g
USB interface	USB 2.0 type B, mini
Note on materials	RoHS-compliant
Housing material	PA6-reinforced
Area of application	Only with CMMT, CPX-E-CEC
Dimensions W x L x H	50 mm x 45 mm x 19.6 mm