

Proximity sensors DADG-D-F8-40

Part number: 8072859

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Symbol	00991702
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Note on materials	RoHS compliant
Rated operating distance	0.6 mm
Assured operating distance	0.64 mm
Reduction factors	Aluminum = 0.55 Stainless steel St 18/8 = 0.8 Copper = 0.5 Brass = 0.65 Steel St 37 = 1.0
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy	0.01 mm
Switching output	PNP
Switching element function	N.O. contact
Max. switching frequency	5000 Hz
Max. switching frequency DC	5000 Hz
Max. output current	100 mA
Voltage drop	2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 30 V
Residual ripple	10%
Idle current	≤10 mA
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Cable length	2 m
Material of cable sheath	TPE-U(PUR)
Size	M4
Type of mounting	Screwed on
Mounting type	Flush
Product weight	32 g
Housing material	Steel
Degree of protection	IP67

Feature	Value
LABS (PWIS) conformity	VDMA24364 Zone III