

Vacuum suction cup OGVM-60-G-N-G14F

Part number: 8073832

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Suction cup height compensation	10.6 mm
Min. workpiece radius	27.5 mm
Nominal width	6 mm
Suction cup diameter	60 mm
Suction cup volume	22 cm ³
Connection position	up
Mounting position	Any
Symbol	00991485
Suction cup shape	Round bell-shaped
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.06 MPa
Nominal operating pressure	-0.6 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-20 °C ... 80 °C
Holding force at nominal operating pressure	143 N
Lateral force at nominal operating pressure	216 N
Product weight	29 g
Type of mounting	Via vacuum connection
Vacuum connection	Internal thread G1/4
Color	Black
Shore hardness	60 +/-5
Material of screwed plug	Wrought aluminum alloy
Note on materials	RoHS compliant
Suction cup material	NBR