

Adapter kit DHAA-G-R3-32-B19-50

Part number: 8079210

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 50 °C
Product weight	70 g
Type of mounting	With internal thread
Adapter plate material	Wrought aluminum alloy, anodized
Material of screws	Galvanized steel