

Moment compensator DARD-L8-32-S

Part number: 8081467

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Radial deviation +/-	2.5 mm
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Short-term maximum permissible load in direction of force +/-	3000 N
Long-term maximum permissible load in direction of force +/-	1500 N
Product weight	294 g
Note on materials	RoHS-compliant Copper-free
Adapter material	Aluminum, anodized
Material of screws	Steel, galvanized