

Cover kit VAVC-F12-SCC-32-TP

Part number: 8084034

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width DN	32
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
LABS (PWIS) conformity	VDMA24364 zone III
Medium	Vapor Hydraulic fluid based on mineral oil Inert gas Mineral oil Water Filtered compressed air, 200 µm filter mesh Neutral liquids
Information on medium	Gaseous media are only permitted with inflow via valve seat.
Temperature of medium	-30 °C ... 200 °C
Ambient temperature	0 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Mounting position	Any
Product weight	424 g
Note on materials	RoHS-compliant
Cover material	High-alloy stainless steel
Spindle seal material	PTFE
Seat seal material	PTFE, modified