


Gear unit EMGA-80-A-G5-100A

Part number: 8085349

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Gearbox flange size	80 mm
Motor flange size	100 mm
Torsional backlash	0.22 deg
Gearbox type	Miter gears
Gear ratio	5:1
Max. actuator speed	7000 rpm
Gearbox operating temperature	-25 °C ... 90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Continuous output torque	67 Nm
Mass moment of inertia, gearbox	1.017 kgcm ²
Max. output torque	107 Nm
Max. efficiency	95 %
Torsional rigidity	4.8 Nm/arcmin
Product weight	4500 g
Permissible axial shaft load	1000 N
Permissible radial shaft load	750 N
Gearbox interface, output shaft	80G
Gearbox interface, actuator	100A
Note on materials	RoHS compliant