

# Pressure regulator VRPA-LM-R18-Q4

Part number: 8086009

FESTO



 General operating condition

## Data sheet

Feature	Value
Controller function	Constant output pressure With secondary exhausting With return flow characteristic
Pneumatic connection 1	R1/8
Pneumatic connection 2	QS-4
Type of mounting	Screw-in
Normal nominal flow rate (normalized to DIN 1343)	90 l/min
Ambient temperature	0 °C ... 60 °C
Housing material	PBT
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Mounting position	Any
Actuation type	Manual
Type of seal on screwed plug	Coating
Adjusting element	Rotary knob with latch
Symbol	00991558
Rotatability	360 deg/continuous swiveling not permissible
Pressure gauge	with pressure gauge
Pressure regulation range MPa	0.1 MPa ... 0.8 MPa
Pressure regulation range	1 bar ... 8 bar
Pressure regulation range psi	14.5 psi ... 116 psi
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1
Product weight	29 g
Material of screwed plug	Brass, nickel-plated
Note on materials	RoHS compliant
Material of threaded seal	PTFE
Static seal material	NBR