

Manifold block VABS-P4-10S-G14

Part number: 8087327

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	21 mm
Mounting position	Any
Structural design	Lateral connection direction
Max. no. of valve positions	1
Operating pressure	0 bar ... 10 bar
Operating medium	Inert gases Air
Information on operating and pilot media	Operation with oil lubrication not possible Maximum particle size 10 µm
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-40 °C ... 80 °C
Temperature of medium	5 °C ... 50 °C
Ambient temperature	5 °C ... 50 °C
Product weight	70 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS compliant
Material of sub-base	Wrought aluminum alloy, anodized