

Manifold block VABS-P4-20S-G38

Part number: 8087328

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	25 mm
Mounting position	Any
Structural design	Connection direction at side
Max. no. of valve positions	1
Operating pressure	0 bar ... 7 bar
Operating medium	Inert gas Air
Information on operating and pilot media	Operation with oil lubrication not possible Maximum particle size 10 µm
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-40 °C ... 80 °C
Temperature of medium	5 °C ... 50 °C
Ambient temperature	5 °C ... 50 °C
Product weight	97 g
Type of mounting	With through-hole
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy, anodized