

Stroke reduction VAVA-F12-H-H1

Part number: 8089993

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Structural design	Opening stroke limitation
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Application note	In case of use with angle seat valve VZXA, the SIL license on the overall product is invalidated.
Degree of protection	IP6X
Ambient temperature	-50 °C ... 100 °C
Storage temperature	-10 °C ... 60 °C
Mounting position	Any
Product weight	253 g
Note on materials	RoHS-compliant
Seals material	EPDM
Nut material	High-alloy stainless steel
Material of screws	High-alloy stainless steel
Shock absorber material	High-alloy steel
Connector material	High-alloy stainless steel