

Parallel kit EAMM-U-65-T42-60PA-87

Part number: 8091225

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------|------------------------|
| Size | 65 |
| Center-to-center distance | 87 mm |
| Mounting position | Any |
| Gear ratio | 1:1 |
| Max. rotational speed | 3000 rpm |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -20 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | 0 °C ... 50 °C |
| Mass moment of inertia | 41.2 kgmm ² |
| No-load driving torque | 0.22 Nm |
| Transferable torque | 3 Nm |
| Product weight | 600 g |
| Interface code, actuator | T42 |
| Interface code, motor in | 60PA |
| Note on materials | RoHS-compliant |