

Memory card CAMC-M-MS-G32-G2

Part number: 8094425

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-25 °C ... 85 °C
Note on materials	RoHS-compliant
Storage capacity	3.2E10 byte
Application note	The device was developed, designed and built exclusively for industrial and commercial applications. The device has not been approved for private use.
Design	microSDHC
Structural design	MLC
Speed class	Class 10
Max. read speed	70 MB/s
Max. write speed	50 MB/s
Number of write/delete cycles	96 TBW