

# Ball valve

## VZBE-3/4-T-63-T-2-F0304-M-V15V15

Part number: 8096666

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature                                                                 | Value                                                                                          |
|-------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|
| Structural design                                                       | 2-way ball valve                                                                               |
| Actuation type                                                          | Mechanical                                                                                     |
| Sealing principle                                                       | Soft                                                                                           |
| Mounting position                                                       | Any                                                                                            |
| Type of mounting                                                        | Line installation                                                                              |
| Fitting connection                                                      | 3/4 NPT                                                                                        |
| Switching position indication                                           | Slot direction = flow direction                                                                |
| Flange hole pattern                                                     | F0304                                                                                          |
| Inside diameter                                                         | 20 mm                                                                                          |
| Nominal width DN                                                        | 20                                                                                             |
| Valve function                                                          | 2/2                                                                                            |
| Flow direction                                                          | Reversible                                                                                     |
| Nominal pressure of fitting PN                                          | 63                                                                                             |
| Breakaway torque at differential pressure, nominal pressure, fitting PN | 9 Nm                                                                                           |
| Based on norm                                                           | ISO 5211                                                                                       |
| Symbol                                                                  | 00991458                                                                                       |
| Medium                                                                  | Vapor<br>Compressed air as per ISO 8573-1:2010 [:-:-]<br>Inert gas<br>Water<br>Neutral liquids |
| Temperature of medium                                                   | -20 °C ... 200 °C                                                                              |
| Flow rate Kv                                                            | 15.6 m <sup>3</sup> /h                                                                         |
| Note on materials                                                       | RoHS-compliant                                                                                 |
| LABS (PWIS) conformity                                                  | VDMA24364 zone III                                                                             |
| Housing material                                                        | Cast stainless steel                                                                           |
| Material number of housing                                              | 1.4408                                                                                         |
| Seat seal material                                                      | PTFE, modified                                                                                 |
| Seals material                                                          | FPM<br>PTFE                                                                                    |

| <b>Feature</b>                      | <b>Value</b>                                                       |
|-------------------------------------|--------------------------------------------------------------------|
| Ball material                       | Cast stainless steel                                               |
| Material number for ball            | 1.4408                                                             |
| Shaft material                      | High-alloy stainless steel                                         |
| Material number for shaft           | 1.4401                                                             |
| Product weight                      | 700 g                                                              |
| Certification                       | CRN                                                                |
| Explosion prevention and protection | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Corrosion resistance class (CRC)    | 4 - Particularly high corrosion stress                             |