

# Clamping sleeve EAMH-145-22-C34-P

Part number: 8098589

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	145
Mounting position	Any
Max. rotational speed	4000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	35.1 kgmm <sup>2</sup>
Product weight	252 g
Note on materials	RoHS-compliant