

# Position indicator SAMH-F12-MK-A2

Part number: 8101084

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Structural design	2 proximity switches with explosion protection and high IP protection
Explosion prevention and protection	Zone 2 (ATEX) Zone 22 (ATEX)
Application note	In case of use with angle seat valve VZXA, the SIL license on the overall product is invalidated.
Note on materials	RoHS-compliant
Ambient temperature	-20 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Product weight	151 g
Seals material	EPDM
Housing material	Aluminum PA-reinforced
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III