

# Axial kit EAMM-A-P8-38A-60R

Part number: 8105916

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	11.8 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	5.87 kgmm <sup>2</sup>
Transferable torque	12.5 Nm
Product weight	145 g
Interface code, actuator	P8-38A
Interface code, motor in	60R
Interface code, coupling housing	38A
Note on materials	RoHS-compliant