


Axial kit EAMM-A-D60-84AA

Part number: 8105945

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------|------------------|
| Nominal length | 75 mm |
| Mounting position | Any |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Transferable torque | 21 Nm |
| Product weight | 1190 g |
| Interface code, actuator | D60 |
| Interface code, motor in | 84AA |
| Note on materials | RoHS-compliant |