

Parallel kit EAMM-U-50-D19-38AA-78

Part number: 8107032

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------|------------------------|
| Size | 50 |
| Mounting position | Any |
| Gear ratio | 1:1 |
| Max. rotational speed | 6000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 12.1 kgmm ² |
| No-load driving torque | 0.01 Nm |
| Transferable torque | 1 Nm |
| Product weight | 600 g |
| Interface code, actuator | D19 |
| Interface code, motor in | 38AA |
| Note on materials | RoHS-compliant |