

Push-in fitting NPQE-D-M3-Q3-P10

Part number: 8112906

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Mini
Nominal width	1 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Straight design
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 0.8 MPa
Operating pressure for entire temperature range	-0.95 bar ... 8 bar
Operating pressure for entire temperature range	-13.775 psi ... 116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Cleanroom suitability, measured according to ISO 14644-14	Class 4 according to ISO 14644-1
Ambient temperature	-5 °C ... 60 °C
Nominal tightening torque	0.3 Nm
Tolerance for nominal tightening torque	±5%
Product weight	1.09 g
Type of mounting	External hexagon AF5.5
Pneumatic connection 1	External thread M3
Pneumatic connection 2	for pneumatic tubing outside diameter 3 mm
Releasing ring color	Blue
Note on materials	RoHS compliant
Housing material	Brass, nickel-plated
Material of threaded seal	NBR
Releasing ring material	POM
O-ring material	NBR
Material of tubing seal	NBR
Material of tube retaining claw	Stainless steel