

# Safety clip NPAP-QE-S-Q10-P10

Part number: 8113231

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Pack size	10
Mounting position	Any
Operating pressure for entire temperature range	-0.095 MPa ... 0.8 MPa
Operating pressure for entire temperature range	-0.95 bar ... 8 bar
Operating pressure for entire temperature range	-13.775 psi ... 116 psi
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-5 °C ... 60 °C
Product weight	0.23 g
Pneumatic connection	For pneumatic tubing outside diameter 10 mm
Note on materials	RoHS compliant