

Solenoid coil VACC-S18-120-K4-2U-NE4ME

Part number: 8118260

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Switching position indication	No
Duty cycle	100%
Insulation class	H
Coil characteristics	110 V AC: 50/60 Hz, power 12.0 VA 110 V DC: 12.0 W
Permissible voltage fluctuations	-15% / +10%
Explosion protection certification outside the EU	EPL Db (CN) EPL Gb (CN)
Explosion prevention and protection	Zone 1 (CN) Zone 21 (CN)
Certificate issuing authority	GYJ23.1169X
Type of ignition protection for gas	Ex eb mb IIC T4 Gb
Type of (ignition) protection for dust	Ex tb IIIC T120°C Db
Explosive ambient temperature	T4, T120°C: -25°C ≤ Ta ≤ +40°C
LABS (PWIS) conformity	VDMA24364 Zone III
Degree of protection	IP66
Product weight	580 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Note on materials	RoHS compliant