

Solenoid coil VACC-S18-35-K4-1U-KS4ME

Part number: 8118317

FESTO



 General operating condition

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Switching position indication	no
Duty cycle	100%
Insulation class	H
Coil characteristics	24 V DC: 3.5 W 24 V AC: 50/60 Hz, power 3.5 VA
Permissible voltage fluctuations	-15 % / +10 %
Explosion protection certification outside the EU	EPL Db (KR) EPL Gb (KR)
Explosion prevention and protection	Zone 1 (KR) Zone 21 (KR)
Certificate issuing authority	22-AV4BO-0256X 22-AV4BO-0257X
Type of ignition protection for gas	Ex e mb IIC T5, T6
Type of (ignition) protection for dust	Ex tD A21 IP66 T85/T95°C
Explosive ambient temperature	T5, T95°C: -25°C ≤ Ta ≤ +60°C T6, T80°C: -25°C ≤ Ta ≤ +50°C
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP66
Product weight	580 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Note on materials	RoHS-compliant