

# Gripper jaws DHAS-GG-B18-16-A1

Part number: 8119108

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	16 mm
Mounting position	Any
Design	For microwell plates
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 70 °C
Relative air humidity	0 - 100%
Ambient temperature	0 °C ... 40 °C
Product weight	24.4 g
Type of mounting	With internal thread M3
Note on materials	RoHS compliant
Gripper jaw material	high-alloy stainless steel
Cylindrical pin material	Spring steel