

Manifold block VABM-C12-6M-M5-M3-10

Part number: 8122794

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	20 mm
Mounting position	Any
Structural design	Connection direction underneath
Max. no. of valve positions	10
Operating pressure	-0.1 MPa ... 0.7 MPa
Operating pressure	-1 bar ... 7 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:1]
Information on operating and pilot media	Maximum particle size 5 µm
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	5 °C ... 50 °C
Product weight	49.5 g
Type of mounting	With through-hole
Pneumatic connection 1	M5
Pneumatic connection 2	M3
Pneumatic connection 3	M5
Note on materials	RoHS compliant
Manifold rail material	Wrought aluminum alloy