



# Pneumatic valve VOFC-L-M52-M-FN14-FN

Part number: 8122930

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Operating pressure	0.25 MPa ... 0.8 MPa
Operating pressure	2.5 bar ... 8 bar
Operating pressure	36.25 psi ... 116 psi
Degree of protection	IP65
Symbol	00995230
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant