


# Pneumatic valve VOFC-L-M52-M-N14-FN

Part number: 8122931

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

| Feature                             | Value  |
|-------------------------------------|--|
| Operating pressure                  | 0.25 MPa ... 0.8 MPa   |
| Operating pressure                  | 2.5 bar ... 8 bar  |
| Operating pressure                  | 36.25 psi ... 116 psi  |
| Degree of protection                | IP65   |
| Symbol                              | 00995231   |
| Explosion prevention and protection | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Corrosion resistance class (CRC)    | 4 - Particularly high corrosion stress                             |
| LABS (PWIS) conformity              | VDMA24364 zone III   |
| Note on materials                   | RoHS-compliant   |