

Angle kit EHAM-AK-L9-90-L9-90-MR

Part number: 8128215

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|-----------------------------|
| Size | 90 |
| Mounting position | Right |
| Structural design | Standard design |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 3623 g |
| Type of mounting | With through-hole and screw |
| Interface code, base | L9-90 |
| Interface code, layout | L9-90 |
| Note on materials | RoHS-compliant |
| Adapter plate material | Aluminum, anodized |
| Material of screws | Steel, nickel-plated |
| Material of centering elements | High-alloy steel |