

# Coupling EAMC-56-58-20-22

Part number: 8134825

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Diameter of holder 1	20 mm
Diameter of holder 2	22 mm
Size	56
Nominal length	58 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	128 kgmm <sup>2</sup>
Transferable torque	60 Nm
Product weight	281 g
Note on materials	RoHS-compliant